Sciencia Acta Xaveriana An International Science Journal ISSN. 0976-1152



Volume 4 No. 1 pp. 99-102 March 2013

Molecular Structure, First-order Hyperpolarizability Studies of L-Arginine Perchlorate

R. Kirubagaran, S. Arulmozhi and J. Madhavan*

Department of Physics, Loyola College, Chennai - 34

* Corresponding Author: jmadhavang@yahoo.com

Abstract : An organic nonlinear optical (NLO) material L-Arginine Perchlorate, was synthesized by slow evaporation technique. The synthesized material was purified by repeated recrystallization. The grown crystal was characterized by single crystal XRD, FT-IR and UV-Vis NIR techniques. The FT-IR spectrum was recorded for LAPCl crystal and the functional groups were identified. The assignments were made with the help of theoretical information obtained from the Density Functional theory. The first order hyperpolarazibility of LAPCl was also determined. The second harmonic generation (SHG) from the material was confirmed using Nd:YAG laser.

Keywords : Nonlinear Optical, Fourier transform infrared spectroscopy, Uv-Vis-NIR) Second harmonic generation, LAPCL

(Received January 2013, Accepted March 2013)

1. Introduction

In recent years the need for nonlinear optical materials is much more than other materials because of their significant impact on laser technology, optical communication and optical data storage technology [1]. Organic crystals with large nonlinear optical (NLO) effects make them attractive for applications in frequency conversion and optical processing [2, 3]. The importance of amino acids in NLO applications is due to the fact that all the amino acids have chiral symmetry and crystallize in noncentro- symmetric space groups [4]. Many number of natural amino acids are individually exhibiting the nonlinear optical properties because they are

99

characterized by chiral carbons, a proton-donating carboxyl (-COOH) group and the protonaccepting amino (-NH2) group. Thus L-arginine, L- histidine and L-alanine have been exploited for the formation of salts with different organic/inorganic acids. In our present work L- Arginine Perchlorate was grown successfully and characterized.

2. Synthesis and Characterization:

2.1 Synthesis

LARPCL was synthesized from high purity L-arginine (Merck-99%) and perchloric acid (Merck-70%) taken in equimolar ratio. The stoichiometric amounts of the reactants were thoroughly dissolved in deionized water. The reaction involved in the synthesis is as follows :

$$NH_{2} CNHNH (CH_{2})_{3} CH NH_{2}COOH + HClO_{4} \longrightarrow$$
$$NH_{2} CNH_{2}^{+} NH (CH_{2})_{3} CHNH_{3}^{+}COO^{-}. ClO_{4}^{-}$$

The synthesized material was then purified from aqueous solution by recrystallization process.

2.2 Single crystal XRD

In order to obtain the crystal data of LARPCL crystals, single crystal X-ray diffraction studies were carried out using ENRAF NONIUS CAD4-F single crystal X-ray diffractometer with MoK_{α} (λ = 0.71073 Å) radiation. The single crystal XRD data of LARPCL crystal indicates that it crystallizes in orthorhombic system with P2₁2₁2₁ space group.

2.3 FTIR spectral analysis

Figure 1 shows the infrared spectrum of LARPCL recorded in the range $4000 - 400 \text{ cm}^{-1}$ using the Bruker IFS 66V FT-IR spectrometer by potassium bromide pellet technique to confirm the presence of functional groups. It is noted from the spectrum that the bands at 3476 and 3403 cm⁻¹ evidence the presence of weakly hydrogen bonded N-H groups. The band at 3277 cm⁻¹ corresponds to stronger hydrogen bonded N-H groups. The bands at 3062, 2973 2946, 2881, and 2830 cm⁻¹ relate to stretching vibrations of C-H bonds of CH and CH₂ groups. The intense band comprising of peaks near 1636 cm⁻¹ may be assigned to asymmetric

stretching of COO⁻, asymmetric bending of NH_3^+ and NH_2^- bending vibrations. The symmetric bending vibrations of NH_3^+ and COOH groups are positioned at 1490 and 1423 cm¹.

2.4 Optical transmittance and nonlinear optical studies

The optical transmission spectrum of LAPCl single crystal was recorded in the wavelength region of 200-2000 nm using VARIAN CARY 5E spectrometer. The spectrum of LArM crystal is shown in Figure 2. It is evident that the crystal possesses a wide optical transparency window from 390 -1100 nm. It is also clearly indicates that the UV cut-off wavelength lies at 390 nm. The presence of low cut-off wavelength and the wide optical transmission window are the suitable parameters for frequency doubling of laser radiation

2.5 Hyperpolarizability Calculations

The first-order hyperpolarizibility (β_{ijk}) of the novel molecular system of LAPCl was calculated. Hyperpolarizibility is a third rank tensor and strongly depends on the method and basis set used. The calculated first order hyper polarizability (β_{total}) of LAPCL is 2.7524 x10³⁰ esu.




Figure 2. Optical absorption spectrum of LArM

3. Conclusion

Single crystals of LAPCI are conveniently grown by employing slow evaporation technique. XRD studies confirm the structure of grown crystals. The optical absorption spectrum of LArM confirms that the crystals possess higher percentage of transmission over a wide range from 390 -1100 nm. SHG in the crystal was confirmed by NLO test.

References :

- Monaco S.B., Davis L.E., Velsko S.P., Wang F.T. and Eimerl D. (1987), J. Crystal growth, Vol. 85, 252–255.
- [2] Sankar D , P. Praveen Kumar , J. Madhavan *Physica B* , February 2010 , 1233–1238
- [3] Ramesh Kumar G, Gokul Raj S., Mohan R. and Jayavel R., (2005), Crystal Growth & Design, Vol.6, 1308-1310.
- [4] Praveen Kumar P, V. Manivannan, S. Tamilselvan, S. Senthil, M. Victor Antony Raj ,Sagayaraj P , J. Madhavan, Optics Communications, May 2008.
- [5] Kleinman. D. A, *Phys. Rev.* 1977, 126, 1962.